

# Grab Rail Clean Seal with Easy Slider Model No. GRCSES29LH or RH\*

www.asijdmacdonald.com.au freecall 1800 023 441

Date: August 2019





Clean seal fully welded construction is finished in satin stainless steel tubing with double chrome plated innovative flange and cover system. Simple fixing method with a hygienically sealed installation with silicone 'o' ring seals. Designed for the safety, security and convenience of the physically disabled. Easy to install on most building surfaces. Tubing diameter is 32mm.

Includes premium designed durable cast alloy cradle with fully adjustable sliding tension for rail and the handset pivot incorporating a self cleaning slide with anti-rotate feature.

### \*HANDING

Grab rails indicating handing are referenced from the in-situation position (eg the pan or shower) not looking at it. Handing is indicated by the suffix of either LH (Left Hand) or RH (Right Hand) and MUST be specified at time of order.

### FINISH

All exposed surfaces shall have a Satin finish.

## **OPTIONS**

Available in Polished finish. Model No. GRCSES29LH-P or GRCSES29RH-P.

## RECOMMENDED INSTALLATION HEIGHT


To comply with Australian Standards AS 1428.1, grab rails must be fastened a minimum distance of 800mm from the floor, with 600mm of clear space above the rail and to withstand a force of 1100N at any point from any direction.

# WARRANTY

One year.

**Grab Rail GRCSES29** (right hand model shown) shall be Model No. GRCSES29 as supplied by ASI JD MacDonald. (Inverted 'T', 500mm x 200mm horizontal and 1100mm vertical).

Å All ASI JD MacDonald disabled compliant products when installed must be in accordance with AS1428 to ensure the specified product is complying with all washroom specification requirements.





- Effectively sealed to inhibit bacteria
- Easy ¼ turn flange cover installation
- Silicone 'o-ring' seals

